


	250 1000
	5,000 00000000
OEM&ODM	







250ml

44mm

71mm

## **HOW TO USE**

1. Screwing the pump on the bottle tightly



2. Turning the pump head in a Counter-clockwise direction



3. The pump will be opened and raised accordingly




4. Press the pump head to receive your liquid



## **High transparence**

Optimized PET 100% virgin materials, no impurities in finished products.






BPA free and Food grade

It is non-toxic, eco friendly and good quality, good for your brand promotion.

**OEM with Factory price**We can print LOGO, custom color to meet your personalized needs.





view more >>